



B22E724NTN Flexible Copper Braid

By Burndy

Catalog # [B22E724NTN](#)

Tin Plated Ferrules.



General

Catalog Number	B22E724NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
Plating Type	Electro tin plated
UPC	781810281185
UPC 12 Digit	7818102811855

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	1829 mm
Dimension - Length Overall inch	72 in
Length	72 in
Thickness	0.38 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50105148](#)
- [Specifications - B22E724NTN](#)