



B22F124N Flexible Copper Braid

By Burndy
Catalog # [B22F124N](#)

Cu Flexible Braid, 4 Holes 2 Ferrules, 1.75" Spacing, 12" L, 1100 Amps.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810049983
UPC 12 Digit	7818100499833

Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Length	12 in

Electrical Ratings

Rating - Outdoor Amperage	1100
---------------------------	------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - B22F124N_MODEL-IGES](#)
[3D Models - B22F124N_MODEL-STEP](#)
[3D Models - B22F124N_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - se212603-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B22F124N-SPEC-EN | REV 1/2024