



## B22F174N Flexible Copper Braid

By Burndy  
Catalog # [B22F174N](#)

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810061084
UPC 12 Digit	7818100610844

### Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	432 mm
Dimension - Length Overall inch	17 in
Length	17 in

### Electrical Ratings

Rating - Outdoor Amperage	1100 A
---------------------------	--------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	192

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - se212603-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B22F174N-SPEC-EN | REV 5/2024