



## B22F17D194N Flexible Copper Braid

By Burndy

Catalog # [B22F17D194N](#)

Flexible Copper Braid.



### General

Catalog Number	B22F17D194N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810061091
UPC 12 Digit	7818100610911

### Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	437 mm
Dimension - Length Overall inch	17.19 in
Length	17.19 in

### Electrical Ratings

Rating - Outdoor Amperage	1100 A
---------------------------	--------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	192

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se212603-01](#)
- [Specifications - B22F17D194N](#)