



B22F17D314N Flexible Copper Braid

By Burndy

Catalog # [B22F17D314N](#)

Flexible Copper Braid.



General

Catalog Number	B22F17D314N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810061107
UPC 12 Digit	7818100611077

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	440 mm
Dimension - Length Overall inch	17.31 in
Length	17.31 in

Electrical Ratings

Rating - Outdoor Amperage	1100 A
---------------------------	--------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	192

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se212603-01](#)
- [Specifications - B22F17D314N](#)



A Hubbell brand