



B22F23D374N Flexible Copper Braid

By Burndy
Catalog # [B22F23D374N](#)

Flexible Copper Braid.



General

Catalog Number	B22F23D374N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810061121
UPC 12 Digit	7818100611211

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	594 mm
Dimension - Length Overall inch	23.37 in
Length	23.37 in

Electrical Ratings

Rating - Outdoor Amperage	1100 A
---------------------------	--------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se212603-01](#)
- [Specifications - B22F23D374N](#)