



B22F274N Flexible Copper Braid

By Burndy
Catalog # [B22F274N](#)

Cu Flexible Braid, 4 Holes 2 Ferrules, 1.75" Spacing, 27.00" L, 1100 Amps.



General

Catalog Number	B22F274N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810165218
UPC 12 Digit	7818101652188

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	686 mm
Dimension - Length Overall inch	27 in
Length	27 in

Electrical Ratings

Rating - Outdoor Amperage	1100 A
---------------------------	--------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_B22F-4N_LineArt](#)
[Sales Drawings - se212603-01](#)
[Specifications - B22F274N](#)