

B22F284N Flexible Copper Braid

By Burndy

Catalog # [B22F284N](#)

Cu Braid, 4-NEMA Holes 2 Ferrules, 28.00" L, 1100 Amps, 0.56" Hole Dia.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	B22F284N
Connector Type	Braid
Material	Copper
UPC	781810308448
UPC 12 Digit	7818103084488

Dimensions

Dimension - D inch	3.06 in
--------------------	---------

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	711 mm
Dimension - Length Overall inch	28.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in
Length	28 in

Electrical Ratings

Amperage Rating	1100 A
-----------------	--------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_B22F-4N_LineArt](#)
[Sales Drawings - 50014375](#)
[Specifications - B22F284N](#)