



B22F304N Flexible Copper Braid

By Burndy

Catalog # [B22F304N](#)



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number B22F304N
Connector Type Braid

Material Copper
UPC 781810307373
UPC 12 Digit 7818103073733

Dimensions

Length 30 in

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_B22F-4N_LineArt](#)
[Specifications - B22F304N](#)