

B22G1344NTN Flexible Copper Braid

By Burndy
Catalog # B22G1344NTN

Tinned Copper Braid 134 X 3 X .56.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	B22G1344NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
UPC	781810657416
UPC 12 Digit	7818106574166

Dimensions

Dimension - L Length Overall mm	3404
------------------------------------	------

Dimension - Length Overall inch	134
Dimension - Width inch	3
Dimension - Width mm	76 mm
Length	134 in

Electrical Ratings

Amperage Rating	1300 A
-----------------	--------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	90

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50032574](#)
[Specifications - B22G1344NTN](#)