



B22G244NW Flexible Copper Braid

By Burndy
Catalog # [B22G244NW](#)

Tin Plated Ferrules.



General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 4 |
| Plated | Y |
| UPC | 781810329276 |
| UPC 12 Digit | 7818103292766 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 610 mm |
| Dimension - Length Overall inch | 24.00 in |
| Length | 24 in |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 2250 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B22G244NW-SPEC-EN | REV 5/2024