



## B22G264N Flexible Copper Braid

By Burndy  
Catalog # [B22G264N](#)

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810373323

### Dimensions

Dimension - L Length Overall mm	660
Dimension - Length Overall inch	26
Length	26 in

### Electrical Ratings

Amperage Rating	1300 A
-----------------	--------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10095071](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B22G264N-SPEC-EN | REV 1/2024