



## B22G26G31W Flexible Copper Braid

By Burndy

Catalog # [B22G26G31W](#)

Tin Plated Ferrules.



### General

Catalog Number	B22G26G31W
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810210796

### Dimensions

Dimension - L Length Overall mm	660 mm
Dimension - Length Overall inch	26.00 in
Length	26 in

### Electrical Ratings

Amperage Rating	1200 A
Rating - Outdoor Amperage	1200

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10105858](#)
- [Specifications - B22G26G31W](#)