



B23D124N Flexible Copper Braid

By Burndy
Catalog # [B23D124N](#)

Flexible Copper Braid.



General

| | |
|---------------------------------------|--------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 6 |
| Plated | Y |
| Plating Type | Tin plated |
| UPC | 621945471313 |
| UPC 12 Digit | 0 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Hole Size inch | 0.56 in |
| Dimension - L Length Overall mm | 305 mm |
| Dimension - Length Overall inch | 12 in |
| Length | 12 in |
| Thickness | 0.3 in |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 4 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 360 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50105537](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B23D124N-SPEC-EN | REV 5/2024