



B240, Horizontal Cable Tap to Horizontal Cable Run, 3/0 AWG (Run), 2 AWG (Tap)

By Burndy
Catalog # B240



Mold, Horizontal Cable Tap to Horizontal Cable Run, 3/0 AWG (Run), 2 AWG (Tap), 45 Weld Metal.

Application

For Joining Horizontal Cable Tap To A Horizontal Run Cable

General

EU RoHS Indicator	Yes
Sub Brand	BURNDYWELD
UPC	781810378571
UPC 12 Digit	7818103785711

Conductor Related

Conductor - Copper Str Run	3/0 AWG
Conductor - Copper Str Run Range	3/0 AWG
Conductor - Copper Str Tap	2 AWG
Conductor - Copper Str Tap Range	2 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU C Str-Tap

Certifications and Compliance

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10044340](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B240-SPEC-EN | REV 1/2024