

## B241, Horizontal Cable Tap to Horizontal Cable Run, 4/0 AWG (Run & Tap)

By Burndy  
Catalog # B241



Mold, Horizontal Cable Tap to Horizontal Cable Run, 4/0 AWG (Run & Tap), 150 Weld Metal.

### Application

For Joining Horizontal Cable Tap To A Horizontal Run Cable

### General

Catalog Number	B241
EU RoHS Indicator	Yes
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
UPC	781810378595
UPC 12 Digit	7818103785955

### Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Run</li><li>• CU C Str-Tap</li></ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	480

### Product Assets

[3D Models - B241\\_MODEL-PDF](#)  
[3D Models - B241\\_MODEL-STEP](#)  
[3D Models - B241\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BCC-2\\_LineArt](#)  
[Sales Drawings - 10044340](#)  
[Specifications - B241](#)