



B248, Horizontal Cable Tap to Horizontal Cable Run, 250 kcmil (Run), 4/0 (Tap)

By Burndy
Catalog # B248



Mold, Horizontal Cable Tap to Horizontal Cable Run, 250 kcmil (Run), 4/0 AWG (Tap), 150 Weld Metal.

Application

For Joining Horizontal Cable Tap To A Horizontal Run Cable

General

EU RoHS Indicator	Yes
Sub Brand	BURNDYWELD
UPC	781810378748
UPC 12 Digit	7818103787488

Conductor Related

Conductor - Copper Str Run	250 kcmil
Conductor - Copper Str Run Range	250 kcmil
Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU C Str-Tap

Certifications and Compliance

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10044340](#)



A proud member of the Hubbell Family.