



B249, Horizontal Cable Tap to Horizontal Cable Run, 250 kcmil (Run), 3/0 AWG (Tap)

By Burndy
Catalog # B249

Mold, Horizontal Cable Tap to Horizontal Cable Run, 250 kcmil (Run), 3/0 AWG (Tap), 150 Weld Metal.



Application

For Joining Horizontal Cable Tap To A Horizontal Run Cable

General

EU RoHS Indicator	Yes
Sub Brand	BURNDYWELD
UPC	781810378762
UPC 12 Digit	7818103787622

Conductor Related

Conductor - Copper Str Run	250 kcmil
Conductor - Copper Str Run Range	250 kcmil
Conductor - Copper Str Tap	3/0 AWG
Conductor - Copper Str Tap Range	3/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU C Str-Tap

Certifications and Compliance

Standards - RoHS Compliance CM Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10044340](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B249-SPEC-EN | REV 1/2024