




B2498, Angular Cable Drop to Vertical Steel Pipe, 4/0 AWG, 6" to 10" Pipe

By Burndy
Catalog # B2498

Mold, Angular Cable Drop to Vertical Steel Pipe, 4/0 AWG, 6" to 10" Pipe, 115 Weld Metal.



Application

For Joining End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface

General

EU RoHS Indicator	Yes
Sub Brand	BURNDYWELD
UPC	781810393598
UPC 12 Digit	7818103935988

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Rigid Pipe Size	6 in-10 in
Conductor - Rigid Pipe Size Range	6 in-10 in
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• Pipe Rigid-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10051631](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B2498-SPEC-EN | REV 1/2024