



B24G284NTN Flexible Copper Braid

By Burndy
Catalog # [B24G284NTN](#)

Tin Plated Ferrules.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
Plated	Y
UPC	781810475850

Dimensions

Dimension - L Length Overall mm	711 mm
Dimension - Length Overall inch	28.00 in
Length	28 in

Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	90

Product Assets

[3D Models - B24G284NTN_MODEL-PDF](#)
[3D Models - B24G284NTN_MODEL-STEP](#)
[3D Models - B24G284NTN_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10094911](#)



A proud member of the Hubbell Family.