

# B2D12D50CG1 Flexible Copper Braid

By Burndy  
Catalog # B2D12D50CG1



Flexible Copper Braid.

## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

Catalog Number	B2D12D50CG1
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810466476
UPC 12 Digit	7818104664766

## Dimensions

Dimension - L Length Overall	305
mm	

Dimension - Length Overall	12
inch	
Length	12.5 in
Weight	0.8 lb

## Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	6
-----------------------	---

## Product Assets

- [3D Models - B2D12D50CG1\\_MODEL-IGES](#)
- [3D Models - B2D12D50CG1\\_MODEL-PDF](#)
- [3D Models - B2D12D50CG1\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10086333](#)
- [Specifications - B2D12D50CG1](#)