



B2D12G46 Flexible Copper Braid

By Burndy
Catalog # [B2D12G46](#)

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810174913
UPC 12 Digit	7818101749133

Dimensions

Dimension - D inch	3.12
Dimension - Hole Size inch	0.62
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.72
Dimension - Pad Width inch	0.94
Length	12 in
Weight	1.17 lb

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Sales Drawings - 50057812](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-B2D12G46-SPEC-EN | REV 8/2023