



B2D12G75TN Flexible Copper Braid

By Burndy

Catalog # [B2D12G75TN](#)

Tin Plated Ferrules.



General

Catalog Number	B2D12G75TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810431627
UPC 12 Digit	7818104316277

Dimensions

Dimension - D inch	1.25
Dimension - Hole Size inch	0.44
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.38
Dimension - Pad Width inch	1.25
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10061766](#)
[Specifications - B2D12G75TN](#)