

## B2D14 Flexible Copper Braid

By Burndy  
Catalog # B2D14



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B2D14
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810082836
UPC 12 Digit	7818100828366

### Dimensions

Dimension - D inch	2.5
Dimension - Hole Size inch	0.44
Dimension - L Length Overall mm	356 mm

Dimension - Length Overall inch	14.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	14 in

### Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1800

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30015666](#)  
[Specifications - B2D14](#)