

B2D14N Flexible Copper Braid

By Burndy
Catalog # B2D14N

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B2D14N
Connector Type	Braid
Material	Copper
UPC	781810454664
UPC 12 Digit	7818104546644

Dimensions

Dimension - D inch	3
Dimension - Hole Size inch	0.56
Dimension - L Length Overall mm	356
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	14 in

Certifications And Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30014549](#)
[Specifications - B2D14N](#)