



B2D16N Flexible Copper Braid

By Burndy
Catalog # [B2D16N](#)

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810205310
UPC 12 Digit	7818102053100

Dimensions

Dimension - D inch	3
Dimension - Hole Size inch	0.56
Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	16 in

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30014549](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B2D16N-SPEC-EN | REV 5/2024