



## B2D18 Flexible Copper Braid

By Burndy  
Catalog # B2D18

Flexible Copper Braid.



### General

Catalog Number	B2D18
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810809068
UPC 12 Digit	7818108090688

### Dimensions

Dimension - D inch	2.5
Dimension - Hole Size inch	0.44
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	18 in

### Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30015666](#)  
[Specifications - B2D18](#)