



B2D18D33TNCG1 Flexible Copper Braid

By Burndy
Catalog # [B2D18D33TNCG1](#)

Tin Plated Ferrules.



General

Catalog Number	B2D18D33TNCG1
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810421000
UPC 12 Digit	7818104210000

Dimensions

Dimension - D inch	2
Dimension - L Length Overall mm	466 mm
Dimension - Length Overall inch	18.33 in
Dimension - N inch	0.56
Dimension - Pad Width inch	0.94
Length	18.33 in
Weight	0.89 lb

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	395

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - cwsc34886-01](#)
[Specifications - B2D18D33TNCG1](#)