



B2D18W Flexible Copper Braid

By Burndy
Catalog # [B2D18W](#)

Tin Plated Ferrules.



General

Catalog Number	B2D18W
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810201381
UPC 12 Digit	7818102013811

Dimensions

Dimension - D inch	2.5
Dimension - L Length Overall mm	457
Dimension - Length Overall inch	18
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30015666](#)
[Specifications - B2D18W](#)