

B2D19D42NTNCG1 Flexible Copper Braid

By Burndy
Catalog # B2D19D42NTNCG1

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

| | |
|---------------------------------------|----------------|
| Catalog Number | B2D19D42NTNCG1 |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 2 |
| Plated | Y |
| UPC | 781810421017 |
| UPC 12 Digit | 7818104210177 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 493 mm |
| Dimension - Length Overall inch | 19.39 in |

| | |
|----------------------------|---------|
| Dimension - Pad Width inch | 0.94 |
| Length | 19.4 in |
| Weight | 1.06 lb |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 380 |
| Rating - Outdoor Amperage | 395 |

Certifications And Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[3D Models - B2D19D42NTNCG1_MODEL-IGES](#)
[3D Models - B2D19D42NTNCG1_MODEL-PDF](#)
[3D Models - B2D19D42NTNCG1_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - cwsc34887](#)
[Specifications - B2D19D42NTNCG1](#)