



B2D24U Flexible Copper Braid

By Burndy
Catalog # [B2D24U](#)

Undrilled Ferrules.



General

Catalog Number	B2D24U
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810139875
UPC 12 Digit	7818101398755

Dimensions

Dimension - D inch	2.5
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	24 in

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30015666](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B2D24U-SPEC-EN | REV 6/2024