



B2D25 Flexible Copper Braid

By Burndy
Catalog # [B2D25](#)

Flexible Copper Braid.



General

Catalog Number	B2D25
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810100776
UPC 12 Digit	7818101007766

Dimensions

Dimension - D inch	2.5
Dimension - L Length Overall mm	635 mm
Dimension - Length Overall inch	25.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch Length	0.94 25 in

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30015666](#)
[Specifications - B2D25](#)