



## B2D27N Flexible Copper Braid

By Burndy  
Catalog # [B2D27N](#)

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810206126
UPC 12 Digit	7818102061266

### Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	686 mm
Dimension - Length Overall inch	27.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	27 in

### Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1800

### Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 30014549](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-B2D27N-SPEC-EN | REV 8/2023