



# B2D36TNG89 Flexible Copper Braid

By Burndy  
Catalog # B2D36TNG89

Tin Plated Braid 36 X .63 X .25.



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

Catalog Number	B2D36TNG89
Material - Ferrules	Copper
UPC	621945467064

## Dimensions

Dimension - L Length Overall mm	914
Dimension - Length Overall inch	36

Dimension - Width inch	1.25
Dimension - Width mm	32 mm
Length	36 in

## Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

## Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	5
Pallet Quantity	900

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50072065](#)  
[Specifications - B2D36TNG89](#)



A Hubbell brand