

B2D52G63W Flexible Copper Braid

By Burndy

Catalog # [B2D52G63W](#)



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B2D52G63W
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810114551
UPC 12 Digit	7818101145511

Dimensions

Dimension - D inch	2.88
Dimension - L Length Overall mm	1321 mm

Dimension - Length Overall inch	52.00 in
Dimension - N inch	0.5
Dimension - Pad Width inch	0.94
Length	52 in

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - B2D52G63W_MODEL-PDF](#)
- [3D Models - B2D52G63W_MODEL-IGES](#)
- [3D Models - B2D52G63W_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30023634](#)
- [Specifications - B2D52G63W](#)