



## B2D5D50G82 Tinned flexible copper braid 5.50"x0.94"x0.25"

By Burndy  
Catalog # [B2D5D50G82](#)

Tinned flexible copper braid 5.50"x0.94"x0.25".



### General

Catalog Number	B2D5D50G82
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
UPC	781810538555
UPC 12 Digit	781810538555

### Dimensions

Dimension - L Length Overall mm	140
Dimension - Length Overall inch	5.5
Dimension - Width inch	0.94
Dimension - Width mm	24 mm
Length	5.5 in

### Electrical Ratings

Rating - Indoor Amperage	380 A
Rating - Outdoor Amperage	455 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [3D Models - B2D5D50G82\\_MODEL-STEP](#)
- [3D Models - B2D5D50G82\\_MODEL-PDF](#)
- [3D Models - B2D5D50G82\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - B2D5D50G82](#)