

B2E12TN Flexible Copper Braid

By Burndy
Catalog # B2E12TN

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	B2E12TN
Connector Type	Braid
Material	Copper
Plated	y
UPC	781810508640
UPC 12 Digit	7818105086400

Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	305

Dimension - Length Overall inch	12
Dimension - N inch	0.75
Dimension - Pad Width inch	1.62
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

Product Assets

- [3D Models - B2E12TN_MODEL-IGES](#)
- [3D Models - B2E12TN_MODEL-PDF](#)
- [3D Models - B2E12TN_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30015682](#)
- [Specifications - B2E12TN](#)