



B2E12U Flexible Copper Braid

By Burndy
Catalog # [B2E12U](#)

Undrilled Ferrules.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810129135
UPC 12 Digit	7818101291355

Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - Pad Width inch	1.62
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30015682](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B2E12U-SPEC-EN | REV 5/2024