

## B2E14N Flexible Copper Braid

By Burndy  
Catalog # B2E14N

Flexible Copper Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

|                                       |               |
|---------------------------------------|---------------|
| Catalog Number                        | B2E14N        |
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 2             |
| Plated                                | N             |
| UPC                                   | 781810077979  |
| UPC 12 Digit                          | 7818100779799 |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - D inch              | 3        |
| Dimension - L Length Overall mm | 356 mm   |
| Dimension - Length Overall inch | 14.00 in |

|                            |       |
|----------------------------|-------|
| Dimension - N inch         | 0.62  |
| Dimension - Pad Width inch | 1.62  |
| Length                     | 14 in |

### Electrical Ratings

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 530 |
| Rating - Outdoor Amperage | 635 |

### Certifications And Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | No    |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX    |
| UL Listed                          | No    |

### Logistics

|                       |     |
|-----------------------|-----|
| Carton Quantity       | 10  |
| Minimum Pack Quantity | 10  |
| Pallet Quantity       | 900 |

### Product Assets

- [3D Models - B2E14N\\_MODEL-IGES](#)
- [3D Models - B2E14N\\_MODEL-PDF](#)
- [3D Models - B2E14N\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30015670](#)
- [Specifications - B2E14N](#)