



## B2E15G127TN Flexible tinned copper braid 15.00"x1.62"x0.25"

By Burndy  
Catalog # B2E15G127TN

Flexible tinned copper braid 15.00"x1.62"x0.25".



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B2E15G127TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
UPC	781810543689
UPC 12 Digit	7818105436899

### Dimensions

Dimension - L Length Overall mm	381
Dimension - Length Overall inch	15

Dimension - Width inch	1.62
Dimension - Width mm	41 mm
Length	15 in

### Electrical Ratings

Rating - Indoor Amperage	530 A
Rating - Outdoor Amperage	635 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	960

### Product Assets

- [3D Models - B2E15G127TN\\_MODEL-PDF](#)
- [3D Models - B2E15G127TN\\_MODEL-STEP](#)
- [3D Models - B2E15G127TN\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30026485](#)
- [Specifications - B2E15G127TN](#)