

B2E18 Flexible Copper Braid

By Burndy
Catalog # B2E18



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

General

Catalog Number	B2E18
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810091838
UPC 12 Digit	7818100918388

Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	457 mm

Dimension - Length Overall inch	18.00 in
Dimension - N inch	0.75
Dimension - Pad Width inch	1.62
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30015682](#)
[Specifications - B2E18](#)