



## B2E18NW Flexible Copper Braid

By Burndy  
Catalog # [B2E18NW](#)

Tin Plated Ferrules.



### General

Catalog Number	B2E18NW
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810477632
UPC 12 Digit	7818104776322

### Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	1.62
Length	18 in

### Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [3D Models - B2E18NW\\_MODEL-PDF](#)
- [3D Models - B2E18NW\\_MODEL-STEP](#)
- [3D Models - B2E18NW\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30015670](#)
- [Specifications - B2E18NW](#)