



## B2E22N Flexible Copper Braid

By Burndy  
Catalog # [B2E22N](#)

Flexible Copper Braid.



### General

Catalog Number	B2E22N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810172551
UPC 12 Digit	7818101725511

### Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	559 mm
Dimension - Length Overall inch	22.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	1.62
Length	22 in

### Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30015670](#)  
[Specifications - B2E22N](#)