



B2E30N Flexible Copper Braid

By Burndy
Catalog # B2E30N

Flexible Copper Braid.



General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 2 |
| Plated | Y |
| UPC | 781810276884 |
| UPC 12 Digit | 7818102768844 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - D inch | 3 |
| Dimension - L Length Overall mm | 762 mm |
| Dimension - Length Overall inch | 30.00 in |
| Dimension - N inch | 0.62 |
| Dimension - Pad Width inch | 1.62 |
| Length | 30 in |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 530 |
| Rating - Outdoor Amperage | 635 |

Certifications And Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | Yes |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 375 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE210201-02_DI](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B2E30N-SPEC-EN | REV 5/2024