



B2E45N Flexible Copper Braid

By Burndy
Catalog # B2E45N

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810244333

Dimensions

Dimension - L Length Overall mm	1143
Dimension - Length Overall inch	45
Length	45 in

Electrical Ratings

Rating - Indoor Amperage	530 A
Rating - Outdoor Amperage	635 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30015670](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B2E45N-SPEC-EN | REV 5/2024