



B2E60 Flexible Copper Braid

By Burndy
Catalog # [B2E60](#)

Flexible Copper Braid.



General

Catalog Number	B2E60
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810202548

Dimensions

Dimension - L Length Overall mm	1524 mm
Dimension - Length Overall inch	60.00 in
Length	60 in

Electrical Ratings

Rating - Indoor Amperage	530 A
Rating - Outdoor Amperage	635 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	180

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30015682](#)
- [Specifications - B2E60](#)