

B2F106 Flexible Copper Braid

By Burndy
Catalog # B2F106

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	B2F106
Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	2
UPC	781810466162

Dimensions

Dimension - Hole Size inch	0.56 in
----------------------------	---------

Dimension - L Length Overall mm	2692
Dimension - Length Overall inch	106
Length	106 in
Thickness - Pad	0.38 in

Electrical Ratings

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

Certifications And Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B2F106](#)