



## B2F10N Flexible Copper Braid

By Burndy  
Catalog # [B2F10N](#)

Flexible Copper Braid.



### General

Catalog Number	B2F10N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810139943

### Dimensions

Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10.00 in
Length	10 in

### Electrical Ratings

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1680

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE..212512-01](#)
- [Specifications - B2F10N](#)