



## B2F12 Flexible Copper Braid

By Burndy  
Catalog # B2F12

Cu Flexible Braid Jumper, 2 Braids in Ferrules, 2 Holes 2 Ferrules, 1.50" Spacing, 12.00" L, .44" Hole Dia., Amp Rating: 600(Indoor) 720(Outdoor).



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810807057

### Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch Length	1.38 in 12 in

### Electrical Ratings

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BD\\_Lineart](#)  
[Sales Drawings - SE210201-02\\_DI](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B2F12-SPEC-EN | REV 5/2024