



B2F12D25NTN Flexible Copper Braid

By Burndy
Catalog # [B2F12D25NTN](#)

Tin Plated Ferrules.



General

Catalog Number	B2F12D25NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810162842

Dimensions

Dimension - L Length Overall mm	311 mm
Dimension - Length Overall inch	12.25 in
Length	12.25 in

Electrical Ratings

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SE212512-01_A](#)



A proud member of the Hubbell Family.